

DC/DC converters 3–300 Watt 4:1 | 12:1

FEATURES

- EN50155 Railway Approvals
- Extended Temperature range: -40°C to +85°C
- Ruggedized designs, EN61373 compliant for shock & vibration
- Ultra wide input voltage range: 9–36, 18–75, 43–160, 14–160 VDC
- Suitable for Applications in Harsh environment

- RIA 12 Surge Filters
- 3-year warranty

STANDARDS AND DIRECTIVES

- IEC/EN/UL 60950-1
- IEC/EN/UL 62368-1
- EN 45545-2
- RIA 12, NF F 01-510

